



# YB803-76#

## Bathroom cabinet




2 Persons


L752\*W455\*H593MM


### Installation Instructions


Notes: Don't tighten screws completely at first, just in case parts were assembled wrongly and need disassemble. Tighten screws at last when all parts are put together.




#### Disassembly and installation of accessories



|                                                                                                                         |                                                                                                                     |                                                                                                                            |                                                                                                                       |                                                                                                                     |                                                                                                                    |                                                                                                                      |                                                                                                               |
|-------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|
| <b>A</b> 48PCS<br><br>15*10mm        | <b>B</b> 48PCS<br><br>6*28mm     | <b>C</b> 68PCS<br><br>3.5*14mm          | <b>D</b> 20PCS<br><br>3.5*35mm     | <b>E</b> 6PCS<br><br>4*18        | <b>F</b> 3PCS<br><br>Handles  | <b>G</b> 4PCS<br><br>Sponge Mat | <b>H</b> 2PCS<br><br>8mm |
| <b>I</b> 2PCS<br><br>Expansion screw | <b>J</b> 2PCS<br><br>Corner code | <b>K</b> 2PCS<br><br>Three-section Rail | <b>L</b> 4PCS<br><br>Hardware Feet | <b>M</b> 1PCS<br><br>Support Rod | <b>N</b> 2PCS<br><br>Mid bend |                                                                                                                      |                                                                                                               |




11




1PC

12




1PC

13




2PCS

14




2PCS

15




2PCS

16










2PCS

17




2PCS

1




|                                                                                       |       |
|---------------------------------------------------------------------------------------|-------|
| B                                                                                     | 48PCS |
|  |       |
| 6*28mm                                                                                |       |

2



|                      |      |
|----------------------|------|
| <b>K<sub>1</sub></b> | 4PCS |
|                      |      |
| Three-section Rail   |      |


3



|          |      |
|----------|------|
| <b>C</b> | 8PCS |
|          |      |
| 3.5*14mm |      |


|                            |      |
|----------------------------|------|
| <b>K<sub>1</sub></b>       | 4PCS |
|                            |      |
| 12 inch Three-section Rail |      |

4




|         |      |
|---------|------|
| A       | 2PCS |
|         |      |
| 15*10mm |      |

5



|         |      |
|---------|------|
| A       | 4PCS |
|         |      |
| 15*10mm |      |

6




A 2PCS



15\*10mm

7




A 2PCS



15\*10mm

8

Ax10




A 10PCS




15\*10mm

9



Ax6



A 6PCS




15\*10mm



△reversal


10



X2

|                                                                                    |       |                                                                                     |       |                                                                                      |      |                                                                                      |      |
|------------------------------------------------------------------------------------|-------|-------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------|------|--------------------------------------------------------------------------------------|------|
| A                                                                                  | 12PCS | D                                                                                   | 20PCS | E                                                                                    | 4PCS | F                                                                                    | 2PCS |
|  |       |  |       |  |      |  |      |
| 15*10mm                                                                            |       | 3.5*35mm                                                                            |       | 4*18                                                                                 |      | Handles                                                                              |      |





11


K<sub>2</sub>x2

X2



|                                                                                       |      |                                                                                       |      |
|---------------------------------------------------------------------------------------|------|---------------------------------------------------------------------------------------|------|
| C                                                                                     | 8PCS | K <sub>2</sub>                                                                        | 2PCS |
|  |      |  |      |
| 3.5*14mm                                                                              |      | Three-section Rail                                                                    |      |


12




|                                                                                     |       |                                                                                      |      |                                                                                      |      |
|-------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------|------|--------------------------------------------------------------------------------------|------|
| <b>A</b>                                                                            | 10PCS | <b>E</b>                                                                             | 2PCS | <b>F</b>                                                                             | 1PCS |
|  |       |  |      |  |      |
| 15*10mm                                                                             |       | 4*18                                                                                 |      | Handles                                                                              |      |

13





|                                                                                       |      |                                                                                       |      |
|---------------------------------------------------------------------------------------|------|---------------------------------------------------------------------------------------|------|
| <b>C</b>                                                                              | 4PCS | <b>N</b>                                                                              | 2PCS |
|  |      |  |      |
| 3.5*14mm                                                                              |      | Hinge                                                                                 |      |



|                                                                                      |       |                                                                                       |      |                                                                                       |      |
|--------------------------------------------------------------------------------------|-------|---------------------------------------------------------------------------------------|------|---------------------------------------------------------------------------------------|------|
| <b>C</b>                                                                             | 12PCS | <b>M</b>                                                                              | 1PCS | <b>H</b>                                                                              | 2PCS |
|  |       |  |      |  |      |
| 3.5*14mm                                                                             |       | Support Rod                                                                           |      | 8mm                                                                                   |      |

15





|                                                                                       |                                                                                       |
|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>G</b> 4PCS                                                                         | <b>I</b> 2PCS                                                                         |
|  |  |
| Sponge Mat                                                                            | Expansion screw                                                                       |

## SPECIAL TIPS FOR DOOR ALIGNMENT


### CONSEJOS ESPECIALES PARA LA ALINEACIÓN DE PUERTAS

### CONSEILS SPÉCIAUX POUR L'ALIGNEMENT DES PORTES





- A. Lateral adjustment (Moving door left-right) by screw adjusting  
 Ajuste lateral (Puerta móvil de izquierda a derecha) mediante tornillo de ajuste  
 Réglage latéral (porte mobile gauche-droite) par réglage à vis







OR




- B. Vertical adjustment (Moving door up-down) via the slot on the mounting plate  
 Ajuste vertical (Puerta móvil arriba-abajo) a través de la ranura en la placa de montaje  
 Réglage vertical (porte mobile de haut en bas) via la fente sur la plaque de montage



- C. Front-to-back adjustment (Spacing Door Off Cabinet) by slacking the hinge arm mounting screw  
 Ajuste de adelante hacia atrás (espaciado entre la puerta y el gabinete) aflojando el tornillo de montaje del brazo de la bisagra  
 Ajustement d'avant en arrière (espacement de la porte hors de l'armoire) en desserrant la vis de montage du bras de charnière




16



Cx16  
Lx4

|                                                                                      |       |                                                                                      |      |
|--------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------|------|
| C                                                                                    | 16PCS | L                                                                                    | 4PCS |
|  |       |  |      |
| 3.5*14mm                                                                             |       | Hardware Feet                                                                        |      |

17



OK